



The STABILO bike makes you independent and mobile again, giving you the freedom to exercise and a means of transport, for doing daily errands when it suits you

STABILO is much like a normal bicycle, combined with the safety of a third wheel.

The frame is designed to make it easy for you to mount and dismount, and it is a pleasure to ride due to its comfortable suspension and soft saddle.

STABILO is a popular choice among people with mild walking difficulty. The model is available as a disability bike for both children and adults.

The STABILO is renowned for comfort, durability and excellent performance:

- easy to mount and safe to ride
- comfortable suspension and soft saddle
- extremely rugged with a long lifetime (10+ years)
- 7 gears with or without reverse function
- adapted to your special needs and delivered within 2-3 weeks

STABILO models are also available with an electric motor, and all models can be adapted to your special needs.

Standard equipment:

- 7 speed Shimano Nexus
- Differential
- Foot brake
- Hand disc brakes front and back
- Parking brake
- Gel saddle
- Adjustable saddle and handlebar
- Basket, back
- Lock w/ 2 keys
- Rear view mirror
- Schwalbe Pick-Up tyres
- Front and back light (motor version)

STABILO P25

(Front wheel motor)

The STABILO P25 has a speed sensor, which ensures that the motor only operates when you are pedaling. You can choose between 5 levels with respect to how much assistance you require from the motor. For help when starting to pedal, you might want to make use of the built-in walk assist (start help) by turning the throttle (up to max 6 km/h). You can drive this bike alone by means of the assist levels, but you can also use the throttle to “overrule” the current assist level and give full power e.g. when you climb hills or need to pass someone or something quickly. When you let go of the throttle, the control system falls back into the chosen assist level. The motor automatically cuts out at max 25 km/h. With a fully charged battery, the bike has a range of up to 35 km. Depending on how much pedaling you do, chosen assist level as well as wind and road conditions, the range can reach distances well above that level.

The display on the handlebar shows you information such as speed, distance, battery level and assist level. The battery is removable, so charging can be done where you prefer.

STABILO P25 gear options:

7 speed free wheel

7 speed with back pedal and reverse gear



Stabilo P25



Stabilo Small P25



Stabilo P25

DATA:	STABILO	SMALL
Length:	192 cm	165 cm
Width :	75 cm	66 cm
Weight w/o motor:	38 kg	36 kg
Weight w motor :	47 kg	45 kg
User measure, min.		
inside leg :	73 cm	67 cm
User weight, max:	125 kg	125 kg
Mounting/ dismounting height:	21 cm	17 cm
Wheel size:	Front: 24"	20"
	Back: 20"	20"

Motor*:	250W	250W
Battery*:	396Wh standard/692Wh option	
<small>* If installed</small>		

STABILO colour options:

	Matte red
	Matte blue
	Matte green
	Matte grey

PF mobility bikes are painted using an environment-friendly powder lacquer

Stabilo comes either with or without a motor